




## Temperatura ambientale massima consentita [°C]

### Vino bottiglia di 750ml, vini fermi, alc 15%

Capsula Spazio non riempito sopra il livello del liquido (mm)	Alluminio, Stagno					Termoretraibile, Polilaminato					Alucap				
	40	50	60	70	80	40	50	60	70	80	40	50	60	70	80
30 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
35 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
40 °C	X	OK	OK	OK	OK	X	OK	OK	OK	OK	X	OK	OK	OK	OK
45 °C	X	OK	OK	OK	OK	X	X	OK	OK	OK	X	OK	OK	OK	OK



La rimozione dell'ossigeno dal collo della bottiglia è raccomandata prima dell'applicazione di tappi.  
Utilizzare solo per i vini fermi - massima sovrappressione di CO<sub>2</sub> a 20°C non deve superare i 0,5 bar.

### Bevande alcoliche bottiglia di 750ml, alc 40%

Capsula Spazio non riempito sopra il livello del liquido (mm)	Alluminio, Stagno					Termoretraibile, Polilaminato					Alucap				
	40	50	60	70	80	40	50	60	70	80	40	50	60	70	80
30 °C	X	OK	OK	OK	OK	X	OK	OK	OK	OK	X	OK	OK	OK	OK
35 °C	X	X	OK	OK	OK	X	X	OK	OK	OK	X	X	OK	OK	OK
40 °C	X	X	X	OK	OK	X	X	X	X	OK	X	X	X	OK	OK
45 °C	X	X	X	X	OK	X	X	X	X	OK	X	X	X	X	OK

### Olio bottiglia di 750 mm

Capsula Spazio non riempito sopra il livello del liquido (mm)	Alluminio, Stagno					Termoretraibile, Polilaminato					Alucap				
	40	50	60	70	80	40	50	60	70	80	40	50	60	70	80
30 °C	X	X	OK	OK	OK	X	X	OK	OK	OK	X	X	OK	OK	OK
35 °C	X	X	X	OK	OK	X	X	X	OK	OK	X	X	X	OK	OK
40 °C	X	X	X	X	OK	X	X	X	X	OK	X	X	X	X	OK
45 °C	X	X	X	X	OK	X	X	X	X	OK	X	X	X	X	OK

### Aceto bottiglia di 750ml, 5-8% di acido acetico

Capsula Spazio non riempito sopra il livello del liquido (mm)	Alluminio, Stagno					Termoretraibile, Polilaminato					Alucap				
	40	50	60	70	80	40	50	60	70	80	40	50	60	70	80
30 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
35 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
40 °C	X	OK	OK	OK	OK	X	OK	OK	OK	OK	X	OK	OK	OK	OK
45 °C	X	OK	OK	OK	OK	X	X	OK	OK	OK	X	OK	OK	OK	OK

### Acqua bottiglia di 750ml, acqua naturale

Capsula Spazio non riempito sopra il livello del liquido (mm)	Alluminio, Stagno					Termoretraibile, Polilaminato					Alucap				
	40	50	60	70	80	40	50	60	70	80	40	50	60	70	80
30 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
35 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
40 °C	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK	OK
45 °C	X	OK	OK	OK	OK	X	X	OK	OK	OK	X	OK	OK	OK	OK